

## Features:

- Ideal for testing static-control products
- Meets ESD Association Standard 11.11 plus ASTM D-257 and EIA-541
- Measures both resistivity and resistance to ground
- Rugged and reliable for routine factory use
- Fast and simple to use
- 8-hour rechargeable battery
- Selectable scientific notation or 3-place log readouts
- No adjustments required

## The final answer for QA/QC inspection of static-control products

For manufacturers and users of products such as electrostatic shielding bags and static dissipative work surfaces, the Model 272A offers rapid, accurate, dependable measurements of resistivity and resistance to ground.

Simply place the resistive material under the instrument's electrode assembly. One glance at the large digital display will tell you whether the test material meets your specifications.

To measure resistivity ( $\Omega/n$ ), a sample is placed under the electrode assembly and a voltage is applied to the outer of two concentric electrodes resting on the sample. The geometry of the electrode assembly's surface is such that current flows from the outer ring, via the sample, to the inner electrode is a direct indication of the sample's resistivity, which is read on the digital display.

In the resistance-measuring mode, current flows from ground or a second electrode through the resistive material to the measurement electrode.

All test parameters can be preset, so operation is push-button simple. The instrument can be programmed to automatically time out to save battery life.



## Easy to use

Test parameters (resistivity/resistance, test voltage, display mode) only need to be set once before testing multiple samples.

To perform either resistivity or resistance to ground measurements:

1. Place the test material on the supplied Teflon® coated specimen support plate and connect a single test lead to the plate.
2. Set the electrode assembly on the test material.
3. Press POWER ON and read test results on the display.



## Portable Surface Resistivity / Resistance Meter model 272A

### Specifications:

**Resistivity range:**  $8 \times 10^4$  to  $2.0 \times 10^{14} \Omega/\text{n}$   
**Resistance range:**  $8 \times 10^3$  to  $2.0 \times 10^{13} \Omega$   
**Accuracy:**  $\pm 0.1$  decade, typical

#### Resistivity measuring voltage

$8.0 \times 10^4 \Omega/\text{n}$  to  $2.0 \times 10^{13} \Omega/\text{n}$ : 10 volts  
 $1.1 \times 10^6 \Omega/\text{n}$  to  $2.0 \times 10^{14} \Omega/\text{n}$ : 100 volts

#### Resistance measuring voltage

$8.0 \times 10^3 \Omega$  to  $2.0 \times 10^{12} \Omega$ : 10 volts  
 $1.1 \times 10^5 \Omega$  to  $2.0 \times 10^{13} \Omega$ : 100 volts

**Display type:** 16-char. alphanumeric LCD

#### Information shown:

Operating mode, measured W or W/+ in log or scientific notation, applied voltage, low battery indication

**Power:** Rechargeable battery with 100, 120, or 230 VAC adapter/charger supplied

**Battery life:** Up to 8 hours continuous operation per charge

#### Electrode Type:

Guarded-ring-type designed to ASTM D-257

**Weight:** 5 lbs. (2.3 kg)

**Outer electrode ring dimensions:** 2.25 inches (5.7 cm) ID, 0.125 inches (0.32 cm) thick

**Inner electrode disc diameter:** 1.2 inches (3.0 cm)

**Electrode/meter cable length:** 3 feet (0.9 m)

**Meter dimensions:** 2.5 x 6.0 x 6.0 inches (6.4 x 15.2 x 15.2 cm)

**Carrying case dimensions:** 7.8 x 7.3 x 7.5 inches (19.8 x 18.5 x 7.5 cm)

**Total weight:** 12 lbs, 13 oz (5.9 kg)

**Optional Probes:** Model SE0032 Mini Guard Ring Probe  
Model 96163 Point-to-Point Probe

### Calibration:

Monroe Electronics instruments are factory-calibrated prior to shipment. Recalibration should be performed annually, or more frequently if specified by contract or company policy. Your instrument should also be recalibrated any time it has been repaired or tampered with. We are happy to recalibrate your instrument for you at a reasonable cost, or provide information and procedures on calibration upon request.

### Warranty:

Monroe Electronics, Inc., warrants that each instrument and sub-assembly manufactured by them shall be free from defects in material and workmanship for a period of one year after shipment from the factory. This warranty is applicable to the original purchaser only.

### The finest Electrostatic instrumentation and support:

For more than 40 years - ever since we invented the feedback--nulled electrostatic voltmeter, Monroe has been the technology and quality leader in electrostatic detection and measurement instrumentation. Today we offer the world's most complete array of fieldmeters, voltmeters, and resistivity meters. Our customers include the leading makers of photocopiers and laser printers, converters and microelectronics worldwide.

We know you need quality support as well as quality products. We pride ourselves on providing our customers with the most knowledgeable applications and installation support — as well as superior customer service.

### Special use applications:

- **A Surface-to-Ground Measuring Adapter** – Model 96121-1 is included with each instrument allowing measurement of flooring and work surface material in compliance with ASTM F-150, ESD 4.1 and ESD 7.1
- **Volume Resistivity** – meets ASTM D-257, IEC 93 and ESD DS11.12 guidelines for measurement of volume resistivity. Please see Application Note APNE-0002 on our website.
- **Measure Narrow Tape Samples** – Please see Application Note APNE-0004 on our website.



Static Clean International • 15 Adams St., Burlington, MA 01803  
Tel: 781-229-7799 Fax: 781-229-4555 • [www.staticclean.com](http://www.staticclean.com)